

ParticleTrack G400

Real-Time Particle Characterization



METTLER TOLEDO

No part of this publication may be stored in a retrieval system, transmitted, or reproduced in any way, including but not limited to photocopy, photograph, magnetic or other record, without the prior written permission of Mettler-Toledo AutoChem, Inc.

FBRM®, iC Process™, iC FBRM™, PVM™, and iC PVM™ are trademarks of Mettler-Toledo AutoChem, Inc.

Microsoft® and Windows® are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

All other brand and product names are trademarks or registered trademarks of their respective owners.

The information in this publication is provided for reference only. All information contained in this publication is believed to be correct and complete. Mettler-Toledo AutoChem, Inc. shall not be liable for errors contained herein nor for incidental or consequential damages in connection with the furnishing, performance, or use of this material. All product specifications, as well as the information contained in this publication, are subject to change without notice.

This publication may contain or reference information and products protected by copyrights or patents and do not convey any license under the patent rights of Mettler-Toledo AutoChem, Inc., nor the rights of others. Mettler-Toledo AutoChem, Inc. does not assume any liability arising out of any infringements of patents or other rights of third parties.

Mettler-Toledo AutoChem, Inc. makes no warranty of any kind with regard to this manual, including but not limited to the implied warranties of merchantability and fitness for a particular purpose.

04192016

For technical support, email: AutoChemCustomerCare@mt.com

For updates, webinars, and the latest documents: <http://community.autochem.mt.com>

Mettler-Toledo AutoChem, Inc.
7075 Samuel Morse Drive
Columbia, MD 21046

www.mt.com/AutoChem

Tel: + 1 866.333.6822

Fax: +1 410.910.8600

Contents

1 Introduction

2 Intended Use

3 Technical Data

4 Safety Information

5 Supplementary Documentation

6 Product Installation

7 Probe Mounting Options

8 Operating Instructions

9 Best Practices for Routine Operation

10 Troubleshooting

11 Product Maintenance

12 Disposal

1 Introduction

This manual covers specific safety and quality information relating to the ParticleTrack™ G400 with FBRM® (Focused Beam Reflectance Measurement) technology. Throughout this manual, the system is referred to by the name: ParticleTrack G400 or FBRM G400. The ParticleTrack G400 system includes the base unit and probe connected by a flexible armored conduit.

ParticleTrack G400 is a probe-based instrument that is inserted directly into laboratory reactors to track changing particle size and count in real time at full process concentrations. Particles, particle structures, and droplets are monitored continuously, as process parameters vary, providing scientists with the evidence required to deliver consistent particles with the required attributes. A ParticleTrack G400 system has fixed or interchangeable probe options and includes options for a single or dual-system configuration. ParticleTrack G400 dual-system configurations can simultaneously measure two small-scale vessels or points in a process stream. Click the link to see the [FBRM Method of Measurement](#) video (requires internet connection).

www.mt.com/ParticleTrack G400

2 Intended Use

The system includes a power supply, laser and detector modules, and PCBs. The base unit is fitted with a permanently attached flexible armored conduit, which is connected to the process probe. The ParticleTrack G400 system is designed for indoor use.

The system may only be used in safe locations and is not certified for use in hazardous locations.

3 Technical Data

System certifications	CE/NRTL-C Approved, Class 1 Laser Device, Compliant with 21CFR1040.10 and 1040.11 and IEC 60825-1; IPX0
Functional specifications	
Method of Measurement	Focused Beam Reflectance Measurement (FBRM®)
Measurement range	0.5 to 2,000 µm
Scan speed	2 m/s (14 mm probe: 125 Hz) 1.2 m/s (19 mm probe: 75 Hz)

Table 1. System certifications and functional specifications

Base Unit Specifications




Figure 1. System Dimensions—Base unit

Environmental	
Operating humidity range	0 to 85%
Operating temperature range	5 to 35 °C
General	
Material of construction	14 ga Aluminum with Class 3 RoHS-compliant chemical film
Ingress protection	IPX0
Power	100-240 VAC, 50/60 Hz, 1.2A
Weight	3.25 kg [7.17 lb]
Communication interface	USB, 3 m [10 ft] cable
Pollution degree	2
Installation (overvoltage) category	II
PCBs	Fr-4

Table 2. Base unit specifications

Explore Litigation Insights

Docket Alarm provides insights to develop a more informed litigation strategy and the peace of mind of knowing you're on top of things.

Real-Time Litigation Alerts



Keep your litigation team up-to-date with **real-time alerts** and advanced team management tools built for the enterprise, all while greatly reducing PACER spend.

Our comprehensive service means we can handle Federal, State, and Administrative courts across the country.

Advanced Docket Research



With over 230 million records, Docket Alarm's cloud-native docket research platform finds what other services can't. Coverage includes Federal, State, plus PTAB, TTAB, ITC and NLRB decisions, all in one place.

Identify arguments that have been successful in the past with full text, pinpoint searching. Link to case law cited within any court document via Fastcase.

Analytics At Your Fingertips



Learn what happened the last time a particular judge, opposing counsel or company faced cases similar to yours.

Advanced out-of-the-box PTAB and TTAB analytics are always at your fingertips.

API

Docket Alarm offers a powerful API (application programming interface) to developers that want to integrate case filings into their apps.

LAW FIRMS

Build custom dashboards for your attorneys and clients with live data direct from the court.

Automate many repetitive legal tasks like conflict checks, document management, and marketing.

FINANCIAL INSTITUTIONS

Litigation and bankruptcy checks for companies and debtors.

E-DISCOVERY AND LEGAL VENDORS

Sync your system to PACER to automate legal marketing.