

EXHIBIT B

COUNTERCLAIM PLAINTIFFS' AMENDED DOCUMENTARY EXHIBIT LIST

IT	DESCRIPTION	BEG BATES	END BATES	OBJECTIONS
	U.S. Patent No. 6,803,545	DEF_PUB_EDVA000003147	DEF_PUB_EDVA000003157	
	U.S. Patent No. 9,814,265	DEF_PUB_EDVA000025690	DEF_PUB_EDVA000025699	
	U.S. Patent No. 10,104,911	DEF_PUB_EDVA000025700	DEF_PUB_EDVA000025714	
	U.S. Patent No. 10,420,374	DEF_PUB_EDVA000025908	DEF_PUB_EDVA000025933	
	U.S. Patent No. 10,555,556	DEF_PUB_EDVA000025946	DEF_PUB_EDVA000025962	
	File History for U.S. Patent No. 6,803,545	DEF_PUB_EDVA000000001	DEF_PUB_EDVA000000173	
	File History for U.S. Patent No. 9,814,265	DEF_PUB_EDVA000014890	DEF_PUB_EDVA000015566	
	File History for U.S. Patent No. 10,104,911	DEF_PUB_EDVA000015567	DEF_PUB_EDVA000016366	
	File History for U.S. Patent No. 10,420,374	DEF_PUB_EDVA000000174	DEF_PUB_EDVA000001780	
	File History for U.S. Patent No. 10,555,556	DEF_PUB_EDVA000018531	DEF_PUB_EDVA000019660	
	Assignment Documents for U.S. Patent No. 6,803,545	DEF_PUB_EDVA000001781	DEF_PUB_EDVA000001785	
	Assignment Documents for U.S. Patent No. 6,803,545	DEF_PUB_EDVA000001786	DEF_PUB_EDVA000001801	
	Assignment Documents for U.S. Patent No. 9,814,265			
	Assignment Documents for U.S. Patent No. 10,104,911			
	Assignment Documents for U.S. Patent No. 10,420,374			
	Assignment Documents for U.S. Patent No. 10,555,556			
	Product Design NCP	PMP_EDVA00005555	PMP_EDVA00005602	
	pmp.npg concept 01: symmetrical felt-tip system, 12/16/2013	PMP_EDVA00003685	PMP_EDVA00003689	
	PMI Research & Development, PTI Review Meeting, Wedegree Mouthpiece Concept, 12/16/2013	PMP_EDVA00003836	PMP_EDVA00003836	
	PMI Research & Development, PTI Review Meeting, Wedegree Mouthpiece Concept 1	PMP_EDVA00003945	PMP_EDVA00003945	
	Vuse Solo Product Guide	RJREDVA_000001421	RJREDVA_000001422	
	Cartridge Part Section Diagram	RJREDVA_000958932	RJREDVA_000958944	
	Section H. Scientific Studies and Analyses Vuse Solo PMTA	RJREDVA_000961817	RJREDVA_000962152	

COUNTERCLAIM PLAINTIFFS' AMENDED DOCUMENTARY EXHIBIT LIST

IT	DESCRIPTION	BEG BATES	END BATES	OBJECTIONS
	Section E. Labeling Vuse Vibe PMTA	RJREDVA_001019459	RJREDVA_001019481	
	Section H. Scientific Studies and Analyses Vuse Vibe PMTA	RJREDVA_001022559	RJREDVA_001022873	
	Section E. Labeling Vuse Vibe PMTA	RJREDVA_001148431	RJREDVA_001148454	
	Section H. Scientific Studies and Analyses Vuse Vibe PMTA	RJREDVA_001150382	RJREDVA_001150691	
	Section H. Scientific Studies and Analyses Vuse Alto PMTA	RJREDVA_001450878	RJREDVA_001451243	
	Data Sheet, 7/10/2016	RJREDVA_001560506	RJREDVA_001560508	
	Regulatory Submission Support for the Vuse Solo Electronic Nicotine Delivery System (ENDS)	RJREDVA_001614853	RJREDVA_001614868	
	Vuse Vibe capillary material	RJREDVA_001617271	RJREDVA_001617271	
	Vuse Alto Kit Insert	RJREDVA_001617736	RJREDVA_001617650	
	Compilation of Teardown Images	DEF_PUB_EDVA000010975	DEF_PUB_EDVA000010983	
	Compilation of Teardown Images	DEF_PUB_EDVA000010987	DEF_PUB_EDVA000010995	
	Compilation of Teardown Images	DEF_PUB_EDVA000011165	DEF_PUB_EDVA000011175	
	Compilation of Teardown Images	DEF_PUB_EDVA000019666	DEF_PUB_EDVA000020038	
	Teardown Images of Solo G2	DEF_PUB_EDVA000052946	DEF_PUB_EDVA000052946	
	Teardown Photos of VUSE Alto	DEF_PUB_EDVA500000001	DEF_PUB_EDVA500000133	
	Screenshots from Vibe CAD File	RJREDVA_001252813	RJREDVA_001252813	
	Screenshots from Solo G2 CAD File	RJREDVA_001252814	RJREDVA_001252814	
	Screenshots from Solo G1 CAD File	RJREDVA_001252815	RJREDVA_001252815	
	Screenshots from Vibe CAD File	RJREDVA_001526196	RJREDVA_001526196	
	Screenshots from Alto CAD File	RJREDVA_001642024	RJREDVA_001642027	
	VUSE Alto photograph	DEF_PUB_EDVA000011719	DEF_PUB_EDVA000011736	
	VUSE Vibe photograph	DEF_PUB_EDVA000011737	DEF_PUB_EDVA000011754	
	VUSE Solo photograph	DEF_PUB_EDVA000011755	DEF_PUB_EDVA000011771	
	VUSE Vibe photograph	DEF_PUB_EDVA000011772	DEF_PUB_EDVA000011790	
	Alto teardown and testing images	DEF_PUB_EDVA000053760	DEF_PUB_EDVA000053786	
	Vibe teardown and testing images	DEF_PUB_EDVA000053787	DEF_PUB_EDVA000053836	
	Solo teardown and testing images	DEF_PUB_EDVA000053837	DEF_PUB_EDVA000053851	
		DEF_PUB_EDVA000054446	DEF_PUB_EDVA000054468	
	Vibe teardown and testing images	DEF_PUB_EDVA000054484	DEF_PUB_EDVA000054515	
	Testing Equipment	DEF_PUB_EDVA000054469	DEF_PUB_EDVA000054483	

COUNTERCLAIM PLAINTIFFS' AMENDED DOCUMENTARY EXHIBIT LIST

IT	DESCRIPTION	BEG BATES	END BATES	OBJECTIONS
	Device Solutions, RJR: Vuse Solo Plus	RJREDVA_001247675	RJREDVA_001247708	
	JUUL Device - See PPX-016			
	Photo of VUSE Ciro Controller Board with Puff Sensor Removed	DEF_PUB_EDVA000053608	DEF_PUB_EDVA000053608	
	Photo of Ciro Puff Sensor Test Setup	DEF_PUB_EDVA000053606	DEF_PUB_EDVA000053606	
	Image of VUSE Ciro Rest Frequency with Oscilloscope Probe Attached (as approximately 9.091 kHz)	DEF_PUB_EDVA000053656	DEF_PUB_EDVA000053656	
	Image of Oscillation Frequency and Output Signal In Response to Simulated Draw (frequency decreased to approximately 8.547 kHz)	DEF_PUB_EDVA000053657	DEF_PUB_EDVA000053657	
	Image of Oscillation Frequency and Output Signal In Response to Simulated Blow (frequency increased to approximately 9.434 kHz)	DEF_PUB_EDVA000053658	DEF_PUB_EDVA000053658	
	Photo of Alto Puff Sensor Test Board With 45 pF Variable Capacitor/Photo of Alto ASIC on Circuit Board	DEF_PUB_EDVA000053594	DEF_PUB_EDVA000053594	
	Image of Oscillation Frequency in Response to Maximum Capacitance (frequency is approximately 5.983 kHz)	DEF_PUB_EDVA000053651	DEF_PUB_EDVA000053651	
	Image of Oscillation Frequency in Response to Minimum Capacitance (frequency is approximately 13.242 kHz)	DEF_PUB_EDVA000053652	DEF_PUB_EDVA000053652	
	Image of Oscillation Frequency Measured at Baseline (frequency is approximately 9.141 kHz)	DEF_PUB_EDVA000053653	DEF_PUB_EDVA000053653	
	Image of Oscillation Frequency and Output Signal in Response to Simulated Blow (frequency increased to 11.879 kHz)	DEF_PUB_EDVA000053654	DEF_PUB_EDVA000053654	
	Image of Oscillation Frequency and Output Signal In Response to Simulated Draw (frequency decreased to approximately 8.807 kHz)	DEF_PUB_EDVA000053655	DEF_PUB_EDVA000053655	
	Photo of Solo Puff Sensor Test Circuit Board With 45 pF Variable Capacitor/Photo of Solo Puff Sensor ASIC on Circuit Board	DEF_PUB_EDVA000053688	DEF_PUB_EDVA000053688	

COUNTERCLAIM PLAINTIFFS' AMENDED DOCUMENTARY EXHIBIT LIST

IT	DESCRIPTION	BEG BATES	END BATES	OBJECTIONS
	Image of Oscillation Frequency in Response to Maximum Capacitance frequency is approximately 12.114 kHz)	DEF_PUB_EDVA000053659	DEF_PUB_EDVA000053659	
	Image of Oscillation Frequency in Response to Minimum Capacitance (frequency is approximately 28.29 kHz)	DEF_PUB_EDVA000053660	DEF_PUB_EDVA000053660	
	Image of Oscillation Frequency Measured at Baseline (frequency is approximately 17.106 kHz)	DEF_PUB_EDVA000053661	DEF_PUB_EDVA000053661	
	Image of Oscillation Frequency and Output Signal in Response to Simulated Blow (frequency increased to 22.026 kHz)	DEF_PUB_EDVA000053662	DEF_PUB_EDVA000053662	
	Image of Oscillation Frequency and Output Signal in Response to Simulated Draw (frequency decreased to approximately 16.181 kHz)	DEF_PUB_EDVA000053663	DEF_PUB_EDVA000053663	
	Photo of Vibe Puff Sensor ASIC on Circuit Board	DEF_PUB_EDVA000053716	DEF_PUB_EDVA000053716	
	Photo of Vibe Puff Sensor Test Board With 25 pF Variable Capacitor	DEF_PUB_EDVA000053689	DEF_PUB_EDVA000053689	
	Image of Oscillation Frequency in Response to Maximum Capacitance (frequency is approximately 10.615 kHz)	DEF_PUB_EDVA000053664	DEF_PUB_EDVA000053664	
	Image of Oscillation Frequency in Response to Minimum Capacitance (frequency is approximately 17.556 kHz)	DEF_PUB_EDVA000053665	DEF_PUB_EDVA000053665	
	Image of Oscillation Frequency Measured at Baseline (frequency is approximately 15.420 kHz)	DEF_PUB_EDVA000053666	DEF_PUB_EDVA000053666	
	Image of Oscillation Frequency and Output Signal In Response to Simulated Draw (frequency decreased to approximately 14.706 kHz)	DEF_PUB_EDVA000053667	DEF_PUB_EDVA000053667	
	Image of Oscillation Frequency and Output Signal in Response to Simulated Blow (frequency increased to 17.376 kHz)	DEF_PUB_EDVA000053668	DEF_PUB_EDVA000053668	
	Picture of VUSE Alto Mouthpeice, Paragraph 47 of Walbrink Opening Report			

Explore Litigation Insights

Docket Alarm provides insights to develop a more informed litigation strategy and the peace of mind of knowing you're on top of things.

Real-Time Litigation Alerts



Keep your litigation team up-to-date with **real-time alerts** and advanced team management tools built for the enterprise, all while greatly reducing PACER spend.

Our comprehensive service means we can handle Federal, State, and Administrative courts across the country.

Advanced Docket Research



With over 230 million records, Docket Alarm's cloud-native docket research platform finds what other services can't. Coverage includes Federal, State, plus PTAB, TTAB, ITC and NLRB decisions, all in one place.

Identify arguments that have been successful in the past with full text, pinpoint searching. Link to case law cited within any court document via Fastcase.

Analytics At Your Fingertips



Learn what happened the last time a particular judge, opposing counsel or company faced cases similar to yours.

Advanced out-of-the-box PTAB and TTAB analytics are always at your fingertips.

API

Docket Alarm offers a powerful API (application programming interface) to developers that want to integrate case filings into their apps.

LAW FIRMS

Build custom dashboards for your attorneys and clients with live data direct from the court.

Automate many repetitive legal tasks like conflict checks, document management, and marketing.

FINANCIAL INSTITUTIONS

Litigation and bankruptcy checks for companies and debtors.

E-DISCOVERY AND LEGAL VENDORS

Sync your system to PACER to automate legal marketing.